


## **DK262 Rhino-Rack** VA, Aero, Euro & HD crossbar instruction

## **IDENTIFICATION CHART**







VA crossbar AERO crossbar EURO crossbar

HD crossbar

		_				VA Cros		AERU	Crossba	ti l	EURU cros		HD Cross	Dai
			FRONT CROSSBAR						REAR CROSSBAR					
			<b>V</b>		VA VA	AERO EURO	HD		<b>Single</b>		VA VA	AERO EURO	HD	
Vehicle	Date	Crossbar	Front Right Pad/ Clamp	Front Left Pad/ Clamp	Measurement strip length per side	Measurement strip length per side	Measurement Distance ( x )	Foot plate arrow direction	Rear Right Pad/ Clamp	Rear Left Pad/ Clamp	Measurement strip length per side	Measurement strip length per side	Measurement Distance ( x )	Foot plate arrow direction
Suzuki Alto GF 5dr hatch	2009-	1060mm	M282 SUB0150	M281 SUB0150	216mm	106mm	886mm / 34,7/8"	OUT	M284 SUB0256	M283 SUB0256	181mm	71mm	816mm / 32,1/8"	OUT
			Arrow FORWARD				34,770		Arro FORW				JZ, 170	
Nissan Pixo 5dr hatch	2009-	1060mm	M282 SUB0150	M281 SUB0150	216mm	106mm	886mm /	OUT	M284 SUB0256	M283 SUB0256	181mm	71mm	816mm /	OUT
			Arrow FORWARD				34,7/8"		Arrow FORWARD				32,1/8"	




## DK262 Rhino-Rack VA, Aero, Euro & HD crossbar instruction


Measurement A: CENTRE of door jamb to CENTRE arrow of leg foot plate.


Measurement B: CENTRE of Front leg foot plate arrow to CENTRE of Rear leg foot plate arrow.


Carrying capacity: Roof rack is rated to 75kg. Please refer to manufacturers handbook for your vehicles maximum roof load capacity. Always use the lower of the two figures.

If your vehicle is not listed on this fitting instruction please refer to your countries Rhino-Rack web site for the latest information.









VEHICLE	Date	Measurement A	Measurement B	Load Rating (includes racks 5kg/ 11lbs)
Suzuki Alto GF 5dr hatch	2009-	200mm / 7,7/8"	700mm / 27,9/16"	50kg / 110lbs
Nissan Pixo 5dr hatch	2009-	200mm / 7,7/8"	700mm / 27,9/16"	50kg / 110lbs

Document No. R117 Issue Date: 20 December 2013 Page 2 of 2